

# **KARATSTERL**

Purpose - Casting

Advantages - Heat treatable, high tarnish resistance

# **Physical & Mechanical Properties**

Composition		
Ag	92.50%	
Cu	4.55%	
Zn	2.70%	
Au	0.25%	

Density (g/cc)		
10.28		

Hardness (HV)		
As cast	71	
1 stage hardened	81	
2 stage hardened	93	

# **Melting & Casting Instructions**

Temperatures		
Casting	960° - 990° C	1760° - 1814° F
Flask	540° - 650° C	1004° - 1202° F

Process parameters		
Quench Time	20-25 minutes	
Remelting	50% fresh mix	

#### **Heat treatment Instructions**

### (1) 1 Stage Hardening process for medium to high hardness:

Heat the sample at 450° C for 1 hour and air cool.

#### (2) 2 Stage Hardening process for super high hardness:

Stage 1 - Anneal the sample at 700° C for 15 - 25 minutes (depending on the size) & quench in water.

Stage 2 - Heat the sample at 450° C for 1 hour and air cool

**Note:** Cover the object with slurry of Borax / Boric acid paste to protect the surface from discoloration.

### **General Instructions**

- Fluxing: It may be necessary to flux these silver melts. We recommend Boric Acid. Do not use Carbon Containing Fluxes or Charcoal. Skim any surface oxides off the surface before stirring.
- Investment removal: <u>Flouric based</u> investment removers are the best for silicon oxide invisible coating. Use of aggressive acid causes corrosion and surface damage. <u>United's brite cast</u> works very effectively.
- To calculate the weight of the metal needed (in grams), <u>multiply density (gm/cc) with weight of wax</u> (grams). Add 10% of the total weight for button.

**Note:** There are proprietary metals in the formulation which are not included in the composition section.

Technical Assistance: Always available... Call: 1-800-999-3463 / 1-800-999-FINE

E-mail: techteam@unitedpmr.com Web-Site: www.unitedpmr.com